

High intensity - Rare Earth



Preface:

The Eclipse high intensity square grid is very versatile and can be utilised in most powder, granulate & liquid applications for the removal of ferrous and paramagnetic contamination down to sub micron in size.

These units can be manufactured to any size and with any number of rods to meet most application requirements. Due to the grids low profile side frame these units can be installed into existing pipelines or feed hoppers.

Grids are of particular interest to OEM's who wish to incorporate them into their machinery with the minimal amount of re-design and also offering flexibility.

Cleaning:

Due to the high intensity magnetic field, and simple design fixed grids require more effort to clean than the Eclipse 'Easy Clean' design. Remove the grid from it's process position and using a gloved hand push the contamination down each rod which will release the majority of all attracted contamination. For any remaining contamination sticky tape can be used to remove the remaining or very fine contaminants.

Suitable Products:

Dry powders and granulates.

Suitable Locations:




Any vertical or slightly angled process line.

Benefits:


■ Simple to install ■ Reduces 'spark' risk ■ Removes sub micron sized contaminants ■ Meet audit requirements ■ Rare Earth 9,000 Gauss ■

Category:

Secondary.



Technical Data:



Sizes:-

Part N	Length A	Width B	Centres C	No. Rods	Weight Kgs
GM1515	150	150	60	2	3.2
GM2020	200	200	60	3	3.8
GM2525	250	250	55	4	6.2
GM3030	300	300	55	5	8.0
GM3535	350	350	55	6	11.0
GM4040	400	400	55	7	14.8
GM4545	450	450	55	8	19.2
GM5050	500	500	55	9	21.0

Performance:-

Magnetic Performance:

7,000 Gauss - Standard Strength
 9,000 Gauss - High Strength
 11,000 Gauss - Super High Strength

Performance Reading:

On tube surface

Magnetic Material:

Rare Earth Neodymium Iron Boron

Magnet Grade:

N35 & N45 – Inspected & confirmed via hystergaph prior to use

Temperature:

-20° C/ + 90° C

All dimensions in mm

Materials:-

Grid Frame:

316 Grade Stainless Steel

Tubing:

316 Grade Stainless Steel – Aerospace Quality

Other Parts:

316 Grade Stainless Steel

Surface Finish:

Polished to 0.6µm

Options:-

High temperature Samarium Cobalt magnetic material + 250° C

Sizes up to 1000mm Ø

Pharmaceutical specification

Safety relay switch

ATEX certified

